





★ 产品特点: 外圈双挡边, 与滚子不可分离, 内圈单挡边, 可从一端自由脱落





①代号	后置代号	轴承团材质	
		GB	JIS
BNJ HQ-BNJ	E: 内部加强设计 M: 铜保持架	GCr15	SUJ2

内圈单挡边
NJ



安装图





视角标准: 第一视角



型号
HQ-BNJ-205EM
BNJ-205EM

型号		d	D	D ₁	d ₁	B	r ₁ (min)	A	基本额定载荷		极限转速		安装尺寸			重量 Kg (参考)
①代号	②公称规格								动载荷/KN	静载荷/KN	脂润滑	油润滑	D _s (min)	Da (max)	ra (max)	
BNJ (标准型) HQ-BNJ (进口型)	205EM	25	52	43.5	34.7	15	1	31.5	28.7	27	11000	14000	29	47	0.3	
	206EM	30	62	16	40.2	16		37.8	36	35.5	8500	11000	34.6	57.6		0.214
	207EM	35	72	60.7	48.3	17	1.1	44	48.7	48.2	8500	10000	39	65.5	0.296	
	208EM	40	80	18	54.9	18		49.3	51.5	50	7000	9000	46.8	71.6	0.394	
	209EM	45	85	72.1	59.2	19		54.5	61.3	64.1	6700	8000	51.5	78.5	0.424	
	210EM	50	90	77.1	64.2	20		59.5	64.1	69.3	6300	7500	56.5	83.5	0.482	

▲ 1kgf=9.8N
▲ 不承诺此产品品牌



交货期

4天发货

C2 轴承关节轴承
锁紧螺母

