


开式


# 陶瓷轴承



★ 产品特点: 耐药性轴承, 可干式 (不润滑) 使用。无磁, 不受磁铁影响。推荐主要用于蚀刻装置、清洗装置、电镀装置等。



代号	类型	M材质			最高使用温度
		轴圈	保持架	球	
BEC	保持架型	ZrO2	PTFE(聚四氟乙烯)	ZrO2	200° C
BED			PEEK(聚醚醚酮)		
BEJ	满球型		无		350° C



视角标准: 第一视角



型号  
**BEC-6000CE**  
**BED-6300CE**  
**BEJ-6200CE**

代号	公称规格	d	D	B	r1	安装尺寸			重量 g (参考)	
						Ds		dh (max)		
						min	max			
	6800CE		19	5			12.5	17	4	
	6900CE		22	6	0.3	12	13	20	7	
	6000CE	10	26	8			13.5	24	14	
	6200CE		30	9			16	26	25	
	6300CE		35	11	0.6		16.5	31	40	
	6801CE		21	5		14	14.5	19	5	
	6901CE		24	6	0.3		15	22	8	
	6001CE	12	28	8			16	26	17	
	6201CE		32	10	0.6	16	17	28	28	
	6301CE		37	12	1		18	32	46	
	6802CE		24	5		17	17.5	22	5	
	6902CE		28	7	0.3		19	26	12	
	6002CE	15	32	9			19	30	24	
	6202CE		35	11	0.6	19	20	31	35	
	6302CE		42	13	1	20	22.5	37	64	
	6803CE		26	5			19.5	24	5	
	6903CE		30	7	0.3	19	20	28	13	
	6003CE	17	35	10			21	33	32	
	6203CE		40	12	0.6	21	23	36	52	
	6303CE		47	14	1		25.5	42	87	
	6804CE		32	7		22	22.5	30	13	
	6904CE		37	9	0.3		24	35	28	
	6004CE	20	42	12	0.6	24	26	38	52	
	6204CE		47	14	1	25		42	82	
	6304CE		52	15	1.1	26.5	28	45.5	110	
	6805CE		37	7				35	16	
	6905CE		42	9	0.3	27	29	40	32	
	6005CE	25	47	12	0.6	29	30.5	43	61	
	6205CE		52	15	1	30	32	47	99	
	6305CE		62	17	1.1	31.5	36	55.5	180	
	6806CE		42	7			33	40	18	
	6906CE		47	9	0.3	32	34	45	40	
	6006CE	30	55	13	0.6		37	50	89	
	6206CE		62	16	1	35	39	57	150	
	6306CE		72	19	1.1	36.5	42.5	65.5	270	
	6807CE		47	7			37	38	45	21
	6907CE		55	10	0.3	39	40	51	58	
	6007CE	35	62	14		40	42	57	120	
	6207CE		72	17	1		41.5	45	65.5	220
	6307CE		80	21	1.1	43	47	72	360	
	6808CE		52	7	0.3	42	43	50	20	
	6908CE		62	12	0.6	44	45	58	90	
	6008CE	40	68	15	1	45	47	63	150	
	6208CE		80	18	1.1	46.5	51	73.5	280	
	6308CE		90	23	1.5	48	53	82	490	

▲ 1kgf=9.8N



交货期 **4** 天发货

数量	1~50
交货期	4 工作日

C2 轴承 关节轴承 锁紧螺母

BEC  
BED  
BEJ