

Nº 6958A


Alavanca de aperto em alumínio

para fixador vertical nº 6958Ax,
pressão de funcionamento máx. 100 bar.



Nº enc.	Nº do artigo	ØE	R	K	P	X	X1*	Força de aperto de 100 bar [kN]	Peso [g]
324434	6958A-16-01-02	8	2	8	18	18	12	1,3	21
324459	6958A-16-01-03	8	2	8	18	24	12	1,0	23
324475	6958A-16-01-04	8	2	8	18	30	12	0,8	25
322594	6958A-20-00-02	10	2	10	22	18	12	2,0	40
322610	6958A-20-00-03	10	2	10	22	24	12	1,5	43
322636	6958A-20-00-04	10	2	10	22	30	12	1,2	47
322792	6958A-25-00-02	12	4	11	27	24	16	2,6	59
322818	6958A-25-00-03	12	4	11	27	32	16	2,0	66
322834	6958A-25-00-04	12	4	11	27	40	16	1,6	73
322990	6958A-32-00-02	15	4	16	34	30	20	5,3	130
323014	6958A-32-00-03	15	4	16	34	40	20	4,0	144
323030	6958A-32-00-04	15	4	16	34	50	20	3,2	158

* X1 = Comprimento do cabo a 90°



CAD



Nº 6958A


Molde da alavanca de aperto em alumínio

para fixador vertical nº 6958Ax,
pressão de funcionamento máx. 100 bar.



Nº enc.	Nº do artigo	ØE	K	P	X	X1*	Peso [g]
324483	6958A-16-01-05	8	8	18	32	12	26
322651	6958A-20-00-05	10	10	22	32	12	49
322859	6958A-25-00-05	12	11	27	44	16	75
323055	6958A-32-00-05	15	16	34	54	20	165

* X1 = Comprimento do cabo a 90°



CAD

