


**Multiflex SL:**  
Flexible, simple & quick installation.

The SL is made of galvanised steel and is being applied when mechanical protection is needed, but water-tightness is not required. The application fields are steel and aluminium foundry industry, machine- and apparatus-building and the security industry. The SL is excellent to protect cables against metal particles and against rodents.

**Material & Construction:**

**Construction:** Galvanised steel core, square-locked.  
**Temperature:** -55 °C to +300 °C.  
**Colour:** Metal coloured.

**Classification according NEN-EN-IEC 61386:**  
**Compression resistance:** Class 4, Heavy (1250 N).  
**Impact resistance:** Class 4, Heavy (6 J).  
**Tensile strength:** Class 4, Heavy (1000 N).  
**Protection class:** IP 40.



**ANACONDA  
MULTIFLEX**

SL	Diameter		Bending radius		Standard carton		Small carton		Reels		Weight (Kg/m)
	Size (Inch)	Inside (mm)	Outside (mm)	Static (mm)	Dynamic (mm)	Metre	Article No.	Metre	Article No.	Metre	
5/16"	10,1	12,8	50	65	30	107.010.2	-	-	-	-	0,14
3/8"	12,6	15,5	60	85	30	107.012.2	-	-	-	-	0,24
1/2"	16,0	18,9	75	110	30	107.016.2	-	-	-	-	0,26
3/4"	21,0	23,9	90	140	30	107.020.2	-	-	-	-	0,41
1"	26,5	30,0	120	170	30	107.026.2	-	-	-	-	0,55
1.1/4"	35,1	38,7	135	215	30	107.035.2	-	-	-	-	0,63

\* For sizes 1.1/2" and bigger it is advised to use the fully inter-locked product type UIG (see page 1-12).

**CONDUIT  
TYPE  
SL**

The fittings for Multiflex SL are outlined on pages 1-04 and 1-06.



Size SL	Inch	1/4"	5/16"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	4"
Fittings	ISO	M12-M16	M16-M20	M16-M20	M20	M25	M32	M40	M50	M63	M75	M90	M105
	PG	7	9 - 11	11 - 13,5	16	21	29	36	42	48	-	-	-
	NPT	-	-	1/2"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	4"