



Multiflex SLI-316:
Flexible & extra corrosion resistant.

The SLI-316 is made of stainless steel and is being applied when chemical and mechanical protection is needed, high temperatures are involved, and water-tightness is not required. The application fields are steelworks and aluminium foundries, navy and shipbuilding industry.

Classification according NEN-EN-IEC 61386:

Compression resistance: Class 4, Heavy (1250 N).

Impact resistance: Class 4, Heavy (6 J).

Tensile strength: Class 4, Heavy (1000 N).

Protection class: IP 40.

Material & Construction:

Construction: Stainless steel (AISI-316) core, square-locked.

Temperature: -100 °C to +600 °C.

Colour: Metal coloured.



Square locked

**ANACONDA
MULTIFLEX**

**CONDUIT
TYPE
SLI-316**

SLI	Diametre		Bending radius		Standard carton		Small carton		Reels		Weight
Size	Inside	Outside	Static	Dynamic	Metre	Article No.	Metre	Article No.	Metre	Article No.	(Kg/m)
(Inch)	(mm)	(mm)	(mm)	(mm)							
5/16"	10,1	12,8	50	65	30	600.610.2	-	-	-	-	0,15
3/8"	12,6	15,5	60	85	30	600.612.2	-	-	-	-	0,24
1/2"	16,0	18,9	75	110	30	600.616.2	-	-	-	-	0,26
3/4"	21,0	23,9	90	140	30	600.620.2	-	-	-	-	0,41
1"	26,5	30,0	120	170	30	600.626.2	-	-	-	-	0,55
1.1/4"	35,1	38,7	135	215	30	600.635.2	-	-	-	-	0,63

The fittings for Multiflex SLI-316 are outlined on pages 1-05 till 1-09.



Size SLI-316	Inch	1/4"	5/16"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	4"
Fittings	ISO	M12-M16	M16-M20	M16-M20	M20	M25	M32	M40	M50	M63	M75	M90	M105
	PG	7	9 - 11	11 - 13,5	16	21	29	36	42	48	-	-	-
	NPT	-	-	1/2"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	4"