



Multiflex SLI:
Flexible & extra corrosion resistant.

The SLI is made of stainless steel and is being applied when chemical and mechanical protection is needed, high temperatures are involved, and water-tightness is not required. The application fields are steelworks and aluminium foundries, navy and shipbuilding industry.

Classification according NEN-EN-IEC 61386:

Compression resistance: Class 4, Heavy (1250 N).

Impact resistance: Class 4, Heavy (6 J).

Tensile strength: Class 4, Heavy (1000 N).

Protection class: IP 40.

Material & Construction:

Construction: Stainless steel (AISI-304) core, square-locked.

Temperature: -100 °C to +600 °C.

Colour: Metal coloured.



Square locked

**ANACONDA
 MULTIFLEX**

**CONDUIT
 TYPE
 SLI**

SLI	Diametre		Bending radius		Standard carton		Small carton		Reels		Weight (Kg/m)
	Size (Inch)	Inside (mm)	Outside (mm)	Static (mm)	Dynamic (mm)	Metre	Article No.	Metre	Article No.	Metre	
5/16"	10,1	12,8	50	65	30	600.010.2	-	-	-	-	0,15
3/8"	12,6	15,5	60	85	30	600.012.2	-	-	-	-	0,24
1/2"	16,0	18,9	75	110	30	600.016.2	-	-	-	-	0,26
3/4"	21,0	23,9	90	140	30	600.020.2	-	-	-	-	0,41
1"	26,5	30,0	120	170	30	600.026.2	-	-	-	-	0,55
1.1/4"	35,1	38,7	135	215	30	600.035.2	-	-	-	-	0,63

* For sizes 1.1/2" and bigger it is advised to use the fully inter-locked product type UI (see page 1-13).

The fittings for Multiflex SLI are outlined on pages 1-04 and 1-06.



Size SLI	Inch	1/4"	5/16"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	4"
Fittings	ISO	M12-M16	M16-M20	M16-M20	M20	M25	M32	M40	M50	M63	M75	M90	M105
	PG	7	9 - 11	11 - 13,5	16	21	29	36	42	48	-	-	-
	NPT	-	-	1/2"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	4"