



DS3GL

SOLENOID OPERATED DIRECTIONAL VALVE WITH DIGITAL INTERFACE


SERIES 10

SUBPLATE MOUNTING ISO 4401-03

p max **350** bar

Q max **80** l/min

MOUNTING INTERFACE




PERFORMANCES


(obtained with mineral oil with viscosity of 36 cSt at 50°C)

Maximum operating pressure:		
- P - A - B ports	bar	350
- T port		210
		160
Maximum flowrate	l/min	80
Pressure drops Δp -Q	see paragraph 5	
Operating limits	see paragraph 7	
Electrical features	see paragraph 8	
Electrical connection	M12 5 pin male A	
Ambient temperature range	°C	-20 / +50
Fluid temperature range	°C	-20 / +80
Fluid viscosity range	cSt	10 ÷ 400
Fluid contamination degree	according to ISO 4406:1999 class 20/18/15	
Recommended viscosity	cSt	25
Mass:		
single solenoid valve	kg	1,5
double solenoid valve		2


OPERATING PRINCIPLE



HYDRAULIC SYMBOL (typical)



1 - IDENTIFICATION CODE




2 - HYDRAULIC FLUIDS

Use mineral oil-based hydraulic fluids HL or HM type, according to ISO 6743-4. For these fluids, use NBR seals (code N). For fluids HFDR type (phosphate esters) use FPM seals (code V). For the use of other fluid types such as HFA, HFB, HFC, please consult our technical department.


Using fluids at temperatures higher than 80 °C causes a faster degradation of the fluid and of the seals characteristics. The fluid must be preserved in its physical and chemical characteristics.

3 - SPOOL TYPE


Type S*:
2 solenoids - 3 positions
with spring centering





Type SA*:
1 solenoid side A
2 positions (central + external)
with spring centering




Type SB*:
1 solenoid side B
2 positions (central + external)
with spring centering





Type TA:
1 solenoid side A
2 external positions
with return spring





Type TB:
1 solenoid side B
2 external positions
with return spring



Type RK:
2 solenoids - 2 positions
with mechanical retention



Proportional spools
for ECG function



NOTE 1: Hydraulic symbols for S2F and S4F are identical to those of S2 and S4 spools.
Besides the diagrams shown, which are the most frequently used, other special versions are available: please refer to catalogue 41150.

4 - ELECTRONICS FUNCTIONS

4.1 - Versions with IO-Link interface: IOL and IOLG

IOL and IOLG versions take advantages from IO-Link communication, providing different methods for feeding the power supply to the solenoid. These versions are fed 24V DC only. A data register feature is implemented for on / off time for both the solenoids, and for the up-mentioned functions.


The IOL version can operate in ECL and EC2 mode, because the function behaviour is set via bus.

The IOLG version offers the ECG type soft switching function and IO-Link interface. It is only available combined with the reserved spools (see par. 1).

4.2 - ECG (IOLG)


This version It is only available combined with the reserved spools. It enables hydraulic actuators to perform a smooth start and stop by setting times values (200 ÷ 600 ms) for ramp up and ramp down.

Performance limits at par. 7.




4.3 - ECL (IOL)

This version allows to feed the solenoid at the nominal current value for a time sufficient to guarantee the complete valve energizing (200 ms). The current is therefore automatically reduced at holding (approx 60%).



4.4 - EC1 / EC2 (IOL)


This version allows to control the solenoid with a low power signal coming from the PLC.





5 - PRESSURE DROPS Δp -Q

(obtained with viscosity 36 cSt at 50 °C)



ENERGIZED POSITION

SPOOL TYPE	FLOW DIRECTION			
	P→A	P→B	A→T	B→T
	CURVES ON GRAPH			
S1, SA1, SB1	2	2	3	3
S2, SA2, SB2	1	1	3	3
S3, SA3, SB3	3	3	1	1
S4, SA4, SB4	5	5	5	5
S5	2	1	3	3
S6	2	2	3	1
S7, S8	4	5	5	5
S9	2	2	3	3
S10	1	3	1	3
S11	2	2	1	3
S12, S17	2	2	3	3
S18	1	2	3	3
TA, TB	3	3	3	3
TA02, TB02	2	2	2	2
TA23, TB23	3	3		
RK, RK02	2	2	2	2

For pressure drops between A and B lines of S10 spools used in regenerative diagrams, refer to curve 5.

DE-ENERGIZED POSITION

SPOOL TYPE	FLOW DIRECTION				
	P→A	P→B	A→T	B→T	P→T
	CURVES ON GRAPH				
S2, SA2, SB2					2
S3, SA3, SB3			3	3	
S4, SA4, SB4					3
S5		4			
S6				3	
S7, S8			6	6	3
S10	3	3			
S11			3		
S18	4				

6 - SWITCHING TIMES


The values indicated are obtained according to ISO 6403 standard, with mineral oil viscosity 36 cSt at 50°C.

versions	TIMES [ms]	
	ENERGIZING	DE-ENERGIZING
IOL	set via bus	set via bus
EC*, ECL	25 ÷ 75	15 ÷ 25
ECG	200	200

7 - OPERATING LIMITS

The curves define the flow rate operating fields according to the valve pressure of the different versions. The values have been obtained according to ISO 6403 norm with solenoids at rated temperature and supplied with voltage equal to 90% of the nominal voltage. The value have been obtained with mineral oil, viscosity 36 cSt, temperature 50 °C and filtration according to ISO 4406:1999 class 18/16/13.

The limits for TA02 and TA spools refer to the 4-way operation. The operating limits of a 4-way valve in 3-way operation or with port A or B plugged or without flow are shown in the related chart.




SPOOL	CURVE	
	P→A	P→B
S1,SA1,SB1	1	1
S2, SA2, SB2	2	2
S3, SA3, SB3	3	3
S4, SA4, SB4	4	4
S5	5	5
S6	4	6
S7	4	4
S8	4	4
S9	7	7
S10	7	7
S11	4	6
S12	1	1
S17	4	4
S18	5	5

SPOOL	CURVE	
	P→A	P→B
TA, TB	7	7
TA02, TB02	8	8
TA23, TB23	2	2
RK	7	7
RK02	8	8

4-WAY VALVE IN 3-WAY OPERATION


Operating limits of a 4-way valve in 3-way operation or with port A or B plugged or without flow.



SPOOL	CURVE
TA backpr. A; TB backpr. B	1
TA02 backpr. A; TB02 backpr. B	1
TA backpr. B; B backpr. A	2
TA02 backpr. B; TB02 backpr. A	3

SPOOLS FOR ECG AND IOLG FUNCTION

Limits of spools type S1, S12, S2F, S4F, S9, TA12, TB12, C26 and A26 specific for soft-shift valves.



SPOOL	CURVE
S1, S12	1
S2F	2
S4F	4
S9	1
TA12, TB12	3
C26, A26	5

8 - ELECTRICAL FEATURES

8.1 - Solenoids

These are essentially made up of two parts: tube and coil. The tube is threaded into the valve body and includes the armature that moves immersed in oil, without wear. The inner part, in contact with the oil in the return line, ensures heat dissipation. The coil is fastened to the tube by a threaded ring, and can be easily replaced.

Protection from atmospheric agents IEC 60529

The IP protection degree is guaranteed only with both valve and connectors of an equivalent IP degree, correctly connected and installed.

electric connection	electric connection protection	whole valve protection
K6 - 2 pins for junction box	IP65	IP65

SUPPLY VOLTAGE FLUCTUATION	± 10% Vnom
MAX SWITCH ON FREQUENCY	18.000 ins/hr
DUTY CYCLE	100%
ELECTROMAGNETIC COMPATIBILITY (EMC)	In compliance with 2014/30/EU
LOW VOLTAGE	In compliance with 2014/35/EU
CLASS OF PROTECTION Coil insulation (VDE 0580) Impregnation	class H class F

8.2 - Current and absorbed power

The table shows current and power consumption values for each function (values ± 10%).


Function	Power supply [V]	Power consumpt [W]		Current consumpt. [A]		Coil nominal voltage [V]	Resistance at 20°C [Ω]	Coil code
		pulse	continuous	pulse	continuous			
IOL	24	-	24	-	1.9	12	4.5	1903800
IOLG	24	-	24	-	1.9	12		
ECG	24	-	24	-	1.9	12		
ECL	24	28	14	2.7	1.5	12		
EC1	12	-	32	-	2.67	12		
EC2	24	-	31	-	1.29	24	18.6	1903801

8.3 - IOL and IOLG functionS: IO-Link communication


2L- and 1L- are galvanic isolated up to 100 V to avoid earth loops. In IO-Link networks, the length of the connecting cables is limited to 20 metres.

Supply voltage	V DC	24 (from 19 to 30 VDC), ripple max 3 Vpp
IO-Link communication (IOL): Data rate	kBaud	IO-Link Port Class B 230,4
Managed breakdowns		Overload and electronics overheating, cable breakdown, supply voltage failures
Connection		5-pin M12 code A (IEC 61076-2-101), male

8.4 - IOL and IOLG pin table



8.5 - IOL and IOLG on-board electronics diagram



8.6 - IOL e IOLG functions: Led

The valve has 2 two-color LEDs visible from the top cover. They work alternatively.

led	colour	on	flashing
L1	green	-	device linked to Master
	red	device disconnected	device powered, not connected to Master
L2	green	valve ready	-
	red	error	-

8.7 - ECG, ECL, EC1 and EC2 functions: electrical characteristics

Supply voltage: ECG, ECL, EC2 EC1	V DC	24, ripple max 3 Vpp 12, ripple max 3 Vpp
Power consumption	W	1 + solenoid consumption (see par. 8.2)
Fuse protection, external:	A	3
Managed breakdowns		Overload and electronics overheating, supply voltage failures


8.8 - ECG, ECL and EC2 pin table

Pin	Values	Function
1	8 ÷ 24 V DC	Digital command coil B
2	+24 V DC	Solenoid supply voltage
3	NC	-
4	8 ÷ 24 V DC	Digital command coil A
5	0V GND	Supply voltage reference

8.9 - EC1 pin table

Pin	Values	Function
1	8 ÷ 12 V DC	Digital command coil B
2	+12 V DC	Solenoid supply voltage
3	NC	-
4	8 ÷ 12 V DC	Digital command coil A
5	0V GND	Supply voltage reference

8.10 - EC* on-board electronics diagram



8.11 - EC* fuctions: led


The valve has 2 two-color LEDs on the top cover. They work alternatively.

led	colour	on
L1	green	coil A energized
	red	coil A error
L2	green	coil B energized
	red	coil B error

9 - ELECTRIC CONNECTORS

A 5-poles M12 code A female connector is required. It can be ordered separately with code 3491001001. See catalogue 89 000 for details.

10 - OVERALL AND MOUNTING DIMENSIONS






11 - INSTALLATION

Configurations with centering and return springs can be mounted in any position; type RK valves - without springs and with mechanical detent - must be mounted with the longitudinal axis horizontal.

Valve fixing takes place by means of screws or tie rods, with the valve mounted on a lapped surface, with values of planarity and smoothness that are equal to or better than those indicated in the drawing. If the minimum values of planarity and/or smoothness are not met, fluid leakages between valve and mounting surface can easily occur.



12 - SUBPLATES

(see catalogue 51 000)

Type PMMD-AI3G with rear ports 3/8" BSP

Type PMMD-AL3G with side ports 3/8" BSP
