

Dual Thermostat, ETR203

- Description:** Device with two independent thermostats, unlike thermostats with changeover contacts, connected devices can be switched in different temperature ranges. One thermostat with a normally closed contact for regulating heaters, and one with a normally opened contact for regulating cooling devices or signal devices. Sensor element thermostatic bimetal. Mounting clip for 35 mm DIN rail (EN 60715).
- Material:** Plastic according to UL94 V-0.
- Setting range:** 0°C to 60°C. Switching temperature difference less than 7°K, and switching point tolerance $\pm 4^{\circ}\text{K}$.
- Switch capacity:** 240V AC, 10(2)A. 120V AC, 15(2)A. 24V DC, 30W. Value in brackets for inductive load.
- Operating temperature:** -40 to +80°C.
- Service life:** > 100,000 cycles.
- Connection:** Screw terminal for cable (0.5 to 2.5 mm²).
- Protection:** IP 20.
- Approvals:** CE, EAC, cULus_UL Listed.
- Finish:** RAL 7035
- Pack quantity:** 1 piece.



Item no.
ETR203

