




DATE STAMP COMPLETE (SHORT VERSION), EMBOSSED LETTERING

Mounting example



2280.02.



Material:

1.2767, hardened HRC 54±2, ground

Note:

The sleeve and insert can be ordered separately (see ordering example).

Description:

- sleeve with engraving
- adjustable insert with display arrow and year (can be rotated using an ordinary screwdriver)
- metric thread for fixing
- mirror image engraving

Mounting:

Fixing:

Screw in the insert in a clockwise direction until it is flush with the top edge and set to the required position.

Setting:

Set the insert by turning clockwise or anti-clockwise. When correctly set, the insert of a stamp with $d_1 = 6$ mm (.060) is typically a maximum of 0.1 mm above or below the top edge of the sleeve.

Changing:

To change the insert turn it anti-clockwise to remove.

2280.02. Date stamp complete (short version), embossed lettering

d_1	d_2	l	s	a
2.6	1.4	4	0.2	0.3
3	1.5	4	0.2	0.3
4	2.1	5	0.25	0.3
5	3.1	8	0.2	0.4
6	3.1	8	0.2	0.4
8	4.4	10	0.25	0.4
10	5.2	12	0.35	0.4
12	6.2	14	0.35	0.6

Order samples:

Date insert, complete	=	2280.
short version	=	02.
Diameter of guide sleeve		
$d_1 = 5$	=	050.
Sleeve with display:		
Months (1-12)	=	10.
Insert with display: Arrow + year		
(variable) e.g. 2004	=	04
Order No	=	2280.02.050.10.04

Date insert, Sleeve	=	2280.
short version	=	02.
Diameter of guide sleeve		
$d_1 = 5$	=	050.
Sleeve with display:		
Months (1-12)	=	10.
Sleeve	=	1
Order No	=	2280.02.050.10.1

Date insert, Insert	=	2280.
short version	=	02.
Diameter of guide sleeve		
$d_1 = 5$	=	050.
Insert with display: Arrow + year		
(variable) e.g. 2004	=	04.
Insert	=	2
Order No	=	2280.02.050.04.2

