


精密冲裁凹模 无凸缘，毛坯，汽车标准

2605.




2605. 精密冲裁凹模 无凸缘，毛坯，汽车标准

d ₂ / 订购数字	P	l ₁ / (订货字母)	13 (A)	16 (B)	20 (C)	22 (D)	25 (E)	28 (F)	30 (G)	32 (H)	35 (J)	40 (K)
10 / (4)	0.8		●	●	●	●	●	●	●	●	●	
13 / (5)	0.8		●	●	●	●	●	●	●	●	●	
16 / (6)	1.5				●	●	●	●	●	●	●	
20 / (7)	1.5				●	●	●	●	●	●	●	
22 / (8)	1.5				●	●	●	●	●	●	●	
25 / (9)	1.5				●	●	●	●	●	●	●	
32 / (10)	1.5				●	●	●	●	●	●	●	
38 / (11)	1.5				●	●	●	●	●	●	●	●
40 / (12)	1.5					●	●	●	●	●	●	●
45 / (13)	1.5					●	●	●	●	●	●	●
50 / (14)	1.5					●	●	●	●	●	●	●
56 / (15)	1.5					●	●	●	●	●	●	●
63 / (16)	1.5					●	●	●	●	●	●	●
71 / (17)	1.5					●	●	●	●	●	●	●
76 / (18)	1.5						●	●	●	●	●	●
85 / (19)	1.5						●	●	●	●	●	●
90 / (20)	1.5						●	●	●	●	●	●
100 / (21)	1.5						●	●	●	●	●	●

订购示例:

2 6 0 5 . 10 F



订货字母
= (F)
订购数字
= (10)
订购数字
= (5)
订购数字
= (0)
= 26

材料:

HSS

硬度 62 ± 2 HRC

结构:

直径 d₂ 导入部以及表面

直径 P 是为电火花线切割钻出的开始孔。

特别尺寸请咨询