


MATRIX WITH SHOULDER, BLANK, ISO 8977

2607.




2607. Matrix with shoulder, blank, ISO 8977

d ₂ / Order No	d ₃	d ₄	P	I / Order No	I ₁ / (Order Code character)	16 (B)	20 (C)	22 (D)	25 (E)	28 (F)	30 (G)	32 (H)	35 (J)
5 / (1)	8	2.8	0.8	2 (1)		●	●	●	●	●	●	●	●
6 / (2)	9	3.5	1	3 (2)		●	●	●	●	●	●	●	●
8 / (3)	11	4	1	4 (3)		●	●	●	●	●	●	●	●
10 / (4)	13	5.8	1	4 (3) 8 (6)		●	●	●	●	●	●	●	●
13 / (5)	16	8	1.2	5 (4) 8 (6)			●	●	●	●	●	●	●
16 / (6)	19	9.5	1.2	5 (4) 8 (6)			●	●	●	●	●	●	●
20 / (7)	23	12	1.5	8 (6) 12 (8)			●	●	●	●	●	●	●
22 / (8)	25	15	1.5	8 (6) 12 (8)			●	●	●	●	●	●	●
25 / (9)	28	17.3	1.5	8 (6) 12 (8)			●	●	●	●	●	●	●
32 / (10)	35	20.7	1.5	8 (6) 12 (8)			●	●	●	●	●	●	●
38 / (11)	41	27.7	1.5	8 (6) 12 (8)			●	●	●	●	●	●	●
40 / (12)	43	27.7	1.5	8 (6) 12 (8)			●	●	●	●	●	●	●
50 / (14)	53	37	1.5	8 (6) 12 (8)			●	●	●	●	●	●	●

Ordering Code (example):

2607.11E6



Order No
 = (6)
Order Code character
 = (E)
Order No
 = (11)
Order No
 = (7)
Order No
 = (0)
 = 26

Material:

HSS
 Hardness 62 ± 2 HRC

Execution:

Diameter d₂, starting lead and face surfaces ground.
 Diameter P is a bored pilot hole for wire EDM.
 Special dimensions on request.