



冲头 DIN 9844 A 型

220.



材料:

HSS

订购编号 220.3.

硬度:

杆部 64 ± 2 HRC

头部 52 ± 3 HRC

HST

订购编号 220.4.

硬度:

杆部 表面 ≥ 950 HV 0,3

头部 52 ± 3 HRC

材料说明和其他材料见E章开头。

结构:

凸模头部热镦粗,用切入磨削法精磨支承面和凸模柄部。

支承长度: 71, 90, 112 mm。

欲订购其它长度和直径时请向我公司咨询!

220. 冲头 DIN 9844 A 型

d ₁	分级						
	d ₁	d ₃	r	l ₁	71	90	112
2	0.1	3.6	0.2	●	●	●	●
2.3	0.1	4	0.2	●	●	●	●
2.6	0.1	4.5	0.3	●	●	●	●
2.9	0.1	5	0.3	●	●	●	●
3.3	0.1	6	0.3	●	●	●	●
3.6	0.1	7	0.3	●	●	●	●
4.1	0.1	8	0.5	●	●	●	●
4.6	0.1	8.5	0.5	●	●	●	●
5.1	0.1	9	0.5	●	●	●	●
5.5	0.1	9.5	0.5	●	●	●	●
6	0.1	10	0.5	●	●	●	●
6.5	0.5	10.8	0.7	●	●	●	●
7.5	0.5	12	0.7	●	●	●	●
8.5	0.5	13	0.7	●	●	●	●
9.5	0.5	14.5	0.7	●	●	●	●
10.5	0.5	16	1	●	●	●	●
11.5	0.5	18	1	●	●	●	●
13	0.5	20	1	●	●	●	●
15	0.5	22	1	●	●	●	●

订购示例:

冲头 DIN 9844 A 型 = 220.

材料 MAT HSS = 3.

切削刀刃直径 d₁ 5.5 mm = 0550.

长度 l₁ 71 mm = 071

订购编号 = 220.3.0550.071