


# DOWEL PIN WITH INTERNAL EXTRACTING THREAD, ACCORDING TO DIN EN ISO 8735

2361.1.



## Material:

Steel  
Hardness 60 ± 2 HRC

## Execution:

hardened and ground to finest finish

## 2361.1. Dowel pin with internal extracting thread, according to DIN EN ISO 8735

d <sub>1</sub>	d <sub>2</sub>	t <sub>1</sub>	l <sub>2</sub>	r	l <sub>1</sub>	8	10	12	14	16	18	20	22	24	26	28	30	32	36	40	45	50	55	60	70	80	90	100	120
4	M2,5	4.5	1.3	4			•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
5	M3	5	1.7	5		•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
6	M4	6	2.1	6				•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
8	M5	8	2.6	8					•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
10	M6	10	3	10						•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
12	M6	10	3.8	12								•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
14	M8	12	4	14												•	•	•	•	•	•	•	•	•	•	•	•	•	•
16	M8	12	4.7	16																									
20	M10	16	6	20																									

## Ordering Code (example):

Dowel pin with internal extracting thread, according to DIN EN ISO 8735	=	2361.1.
Diameter d <sub>1</sub>	10 mm =	1000.
Length l <sub>1</sub>	16 mm =	016
Order No	=	2361.1. 1000. 016