


Part No. structure



## Series R58 - snap-open along outer radius

Part No.	$B_i$ [mm]	$B_a$ [mm]	$R$ [mm]	Bending radii					Weight [kg/m]
58.050.□.0	50	66	075	100	125	150	200	250	≈ 1,50
58.075.□.0	75	91	075	100	125	150	200	250	≈ 1,77
58.100.□.0	100	116	075	100	125	150	200	250	≈ 2,04
58.125.□.0	125	141	075	100	125	150	200	250	≈ 2,31
58.150.□.0	150	166	075	100	125	150	200	250	≈ 2,61
58.175.□.0	175	191	075	100	125	150	200	250	≈ 2,88
58.200.□.0	200	216	075	100	125	150	200	250	≈ 3,15

Supplement Part No. with required radius. Example: 58.100.□.100.0

0 = standard color, other colors ► page 1.39 · Pitch = 33,3 mm/link - Links/m = 30



Phone +49- (0) 22 03-96 49-800  
Fax +49- (0) 22 03-96 49-222

igus® GmbH  
51147 Cologne

Internet: [www.igus.eu](http://www.igus.eu)  
E-mail: [info@igus.de](mailto:info@igus.de)

## Hot Chips up to 850°C

E-Tubes that repel hot chips, up to 850 °C. Some applications, depending on amount and size of the chips, can burn or melt the surface. That is no longer the case with the igus® "igumid HT" material.

Order example - Full E-Tube made of HT\*: **58.100.100.0.HT**

Order example - Lids made of HT: **58.100HT.100.0**

\*for long travels upon request

**Delivery time up to 4 weeks!** Further Information: [www.igus.de/en/HT](http://www.igus.de/en/HT)

