

d1	d2	b1	d1 ³⁾		Housing bore		Shaft size		Part No.
			Max.	Min.	Max.	Min.	Max.	Min.	
1/2	19/32	1/4	.5030	.5003	.5941	.5934	.4990	.4980	Q2SI-0809-04
1/2	19/32	3/8	.5030	.5003	.5941	.5934	.4990	.4980	Q2SI-0809-06
1/2	19/32	1/2	.5030	.5003	.5941	.5934	.4990	.4980	Q2SI-0809-08
1/2	19/32	5/8	.5030	.5003	.5941	.5934	.4990	.4980	Q2SI-0809-10
1/2	19/32	3/4	.5030	.5003	.5941	.5934	.4990	.4980	Q2SI-0809-12
1/2	19/32	1	.5030	.5003	.5941	.5934	.4990	.4980	Q2SI-0809-16
9/16	21/32	1/2	.5655	.5627	.6566	.6559	.5615	.5605	Q2SI-0910-08
9/16	21/32	5/8	.5655	.5627	.6566	.6559	.5615	.5605	Q2SI-0910-10
9/16	21/32	3/4	.5655	.5627	.6566	.6559	.5615	.5605	Q2SI-0910-12
5/8	23/32	1/2	.6280	.6253	.7192	.7184	.6240	.6230	Q2SI-1011-08
5/8	23/32	3/4	.6280	.6253	.7192	.7184	.6240	.6230	Q2SI-1011-12
5/8	23/32	1	.6280	.6253	.7192	.7184	.6240	.6230	Q2SI-1011-16
3/4	7/8	1/2	.7541	.7505	.8755	.8747	.7491	.7479	Q2SI-1214-08
3/4	7/8	3/4	.7541	.7505	.8755	.8747	.7491	.7479	Q2SI-1214-12
3/4	7/8	1	.7541	.7505	.8755	.8747	.7491	.7479	Q2SI-1214-16
3/4	1	3/4	.7541	.7508	1.0010	1.0000	.7491	.7479	Q2SI-1216-16
7/8	1	1/2	.8791	.8757	1.0005	.9997	.8741	.8729	Q2SI-1416-08
7/8	1	3/4	.8791	.8757	1.0005	.9997	.8741	.8729	Q2SI-1416-12
7/8	1	1	.8791	.8757	1.0005	.9997	.8741	.8729	Q2SI-1416-16
1	1 1/8	1/2	1.0041	1.0007	1.1255	1.1247	.9991	.9979	Q2SI-1618-08
1	1 1/8	3/4	1.0041	1.0007	1.1255	1.1247	.9991	.9979	Q2SI-1618-12
1	1 1/8	1	1.0041	1.0007	1.1255	1.1247	.9991	.9979	Q2SI-1618-16
1	1 1/4	1 1/2	1.0041	1.0007	1.2510	1.2500	.9991	.9979	Q2SI-1620-24
1 1/8	1 1/4	3/4	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	Q2SI-1820-12
1 1/8	1 1/4	1	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	Q2SI-1820-16
1 1/8	1 1/4	1 1/4	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	Q2SI-1820-20
1 1/4	1 13/32	3/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	Q2SI-2022-12
1 1/4	1 13/32	1	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	Q2SI-2022-16
1 1/4	1 13/32	1 1/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	Q2SI-2022-20
1 1/4	1 13/32	1 1/2	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	Q2SI-2022-24
1 1/4	1 1/2	1 1/2	1.2548	1.2508	1.5005	1.4995	1.2488	1.2472	Q2SI-2024-24
1 1/2	1 21/32	1	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	Q2SI-2426-16
1 1/2	1 21/32	1 1/2	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	Q2SI-2426-24
1 1/2	1 3/4	1 1/2	1.5048	1.5008	1.7505	1.7495	1.4988	1.4972	Q2SI-2428-24
1 5/8	1 25/32	1	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	Q2SI-2629-16
1 5/8	1 25/32	1 1/2	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	Q2SI-2629-24
1 3/4	1 15/16	1	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	Q2SI-2831-16
1 3/4	1 15/16	2	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	Q2SI-2831-32
1 7/8	2 1/16	1	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	Q2SI-3033-16
1 7/8	2 1/16	2	1.8747	1.8786	2.0633	2.0621	1.8737	1.8721	Q2SI-3033-32
2	2 3/16	1	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	Q2SI-3235-16
2	2 3/16	2	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	Q2SI-3235-32
2	2 1/4	2 1/4	2.0059	2.0012	2.2505	2.2495	1.9981	1.9969	Q2SI-3236-36

³⁾ After press-fit. Testing methods ► Page 57

iglidur® W300										Chapter ► Page 153	
d1	d2	b1	d1 ³⁾		Housing bore		Shaft size		Part No.		
			Max.	Min.	Max.	Min.	Max.	Min.			
1/8	3/16	3/16	.1269	.1251	.1878	.1873	.1243	.1236	WSI-0203-03		
1/8	3/16	1/4	.1269	.1251	.1878	.1873	.1243	.1236	WSI-0203-04		
1/8	3/16	3/8	.1269	.1251	.1878	.1873	.1243	.1236	WSI-0203-06		
3/16	1/4	1/4	.1892	.1873	.2503	.2497	.1865	.1858	WSI-0304-04		
3/16	1/4	3/8	.1892	.1873	.2503	.2497	.1865	.1858	WSI-0304-06		
3/16	1/4	1/2	.1892	.1873	.2503	.2497	.1865	.1858	WSI-0304-08		
1/4	5/16	3/16	.2521	.2498	.3128	.3122	.2490	.2481	WSI-0405-03		
1/4	5/16	1/4	.2521	.2498	.3128	.3122	.2490	.2481	WSI-0405-04		
1/4	5/16	5/16	.2521	.2498	.3128	.3122	.2490	.2481	WSI-0405-05		
1/4	5/16	3/8	.2521	.2498	.3128	.3122	.2490	.2481	WSI-0405-06		
1/4	5/16	1/2	.2521	.2498	.3128	.3122	.2490	.2481	WSI-0405-08		
5/16	3/8	1/4	.3148	.3125	.3753	.3747	.3115	.3106	WSI-0506-04		
5/16	3/8	3/8	.3148	.3125	.3753	.3747	.3115	.3106	WSI-0506-06		
5/16	3/8	1/2	.3148	.3125	.3753	.3747	.3115	.3106	WSI-0506-08		
5/16	3/8	3/4	.3148	.3125	.3753	.3747	.3115	.3106	WSI-0506-12		
3/8	15/32	1/4	.3773	.3750	.4691	.4684	.3740	.3731	WSI-0607-04		
3/8	15/32	3/8	.3773	.3750	.4691	.4684	.3740	.3731	WSI-0607-06		
3/8	15/32	7/16	.3773	.3750	.4691	.4684	.3740	.3731	WSI-0607-07		
3/8	15/32	1/2	.3773	.3750	.4691	.4684	.3740	.3731	WSI-0607-08		
3/8	15/32	5/8	.3773	.3750	.4691	.4684	.3740	.3731	WSI-0607-10		
3/8	15/32	3/4	.3773	.3750	.4691	.4684	.3740	.3731	WSI-0607-12		
3/8	17/32	3/4	.3773	.3750	.5316	.5309	.3740	.3731	WSI-0608-12		
7/16	17/32	1/4	.4406	.4379	.5316	.5309	.4365	.4355	WSI-0708-04		
7/16	17/32	1/2	.4406	.4379	.5316	.5309	.4365	.4355	WSI-0708-08		
7/16	17/32	3/4	.4406	.4379	.5316	.5309	.4365	.4355	WSI-0708-12		
1/2	19/32	3/16	.5030	.5003	.5941	.5934	.4990	.4980	WSI-0809-03		
1/2	19/32	1/4	.5030	.5003	.5941	.5934	.4990	.4980	WSI-0809-04		
1/2	19/32	3/8	.5030	.5003	.5941	.5934	.4990	.4980	WSI-0809-06		
1/2	19/32	1/2	.5030	.5003	.5941	.5934	.4990	.4980	WSI-0809-08		
1/2	19/32	5/8	.5030	.5003	.5941	.5934	.4990	.4980	WSI-0809-10		
1/2	19/32	3/4	.5030	.5003	.5941	.5934	.4990	.4980	WSI-0809-12		
1/2	19/32	1	.5030	.5003	.5941	.5934	.4990	.4980	WSI-0809-16		
1/2	5/8	1/2	.5040	.5013	.6260	.6250	.5000	.4990	WSI-0810-08		
1/2	5/8	5/8	.5040	.5013	.6260	.6250	.5000	.4990	WSI-0810-10		
1/2	5/8	3/4	.5040	.5013	.6260	.6250	.5000	.4990	WSI-0810-12		
1/2	5/8	1	.5040	.5013	.6260	.6250	.5000	.4990	WSI-0810-16		
9/16	21/32	1/2	.5655	.5627	.6566	.6559	.5615	.5605	WSI-0910-08		
9/16	21/32	5/8	.5655	.5627	.6566	.6559	.5615	.5605	WSI-0910-10		
9/16	21/32	3/4	.5655	.5627	.6566	.6559	.5615	.5605	WSI-0910-12		
5/8	23/32	1/4	.6280	.6253	.7192	.7184	.6240	.6230	WSI-1011-04		
5/8	23/32	3/8	.6280	.6253	.7192	.7184	.6240	.6230	WSI-1011-06		
5/8	23/32	1/2	.6280	.6253	.7192	.7184	.6240	.6230	WSI-1011-08		
5/8	23/32	5/8	.6280	.6253	.7192	.7184	.6240	.6230	WSI-1011-10		
5/8	23/32	3/4	.6280	.6253	.7192	.7184	.6240	.6230	WSI-1011-12		

³⁾ After press-fit. Testing methods ► Page 57

d1	d2	b1	d1 ³⁾		Housing bore		Shaft size		Part No.
			Max.	Min.	Max.	Min.	Max.	Min.	
5/8	23/32	1	.6280	.6253	.7192	.7184	.6240	.6230	WSI-1011-16
11/16	25/32	3/4	.6906	.6879	.7817	.7809	.6865	.6855	WSI-1112-12
3/4	7/8	1/2	.7541	.7507	.8755	.8747	.7491	.7479	WSI-1214-08
3/4	7/8	3/4	.7541	.7507	.8755	.8747	.7491	.7479	WSI-1214-12
3/4	7/8	1	.7541	.7507	.8755	.8747	.7491	.7479	WSI-1214-16
3/4	7/8	1 1/2	.7541	.7507	.8755	.8747	.7491	.7479	WSI-1214-24
7/8	1	1/4	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-04
7/8	1	3/8	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-06
7/8	1	1/2	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-08
7/8	1	5/8	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-10
7/8	1	3/4	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-12
7/8	1	1	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-16
7/8	1	1 1/2	.8791	.8757	1.0005	.9997	.8741	.8729	WSI-1416-24
1	1 1/8	3/8	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-06
1	1 1/8	1/2	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-08
1	1 1/8	3/4	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-12
1	1 1/8	1	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-16
1	1 1/8	1 5/16	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-20
1	1 1/8	1 3/8	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-22
1	1 1/8	1 1/2	1.0041	1.0007	1.1255	1.1247	.9991	.9979	WSI-1618-24
1 1/8	1 1/4	3/4	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	WSI-1820-12
1 1/8	1 1/4	1	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	WSI-1820-16
1 1/8	1 1/4	1 1/4	1.1288	1.1254	1.2818	1.2808	1.1238	1.1226	WSI-1820-20
1 1/4	1 13/32	3/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-12
1 1/4	1 13/32	7/8	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-14
1 1/4	1 13/32	1	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-16
1 1/4	1 13/32	1 1/4	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-20
1 1/4	1 13/32	1 1/2	1.2548	1.2508	1.4068	1.4058	1.2488	1.2472	WSI-2022-24
1 3/8	1 17/32	1	1.3798	1.3758	1.5318	1.5308	1.3738	1.3722	WSI-2224-16
1 3/8	1 17/32	1 1/2	1.3798	1.3758	1.5318	1.5308	1.3738	1.3722	WSI-2224-24
1 1/2	1 21/32	3/4	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	WSI-2426-12
1 1/2	1 21/32	1	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	WSI-2426-16
1 1/2	1 21/32	1 1/2	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	WSI-2426-24
1 1/2	1 21/32	2 3/4	1.5048	1.5008	1.6568	1.6558	1.4988	1.4972	WSI-2426-44
1 5/8	1 25/32	1	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	WSI-2629-16
1 5/8	1 25/32	1 1/4	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	WSI-2629-20
1 5/8	1 25/32	1 1/2	1.6297	1.6258	1.7818	1.7808	1.6238	1.6222	WSI-2629-24
1 3/4	1 15/16	1	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	WSI-2831-16
1 3/4	1 15/16	1 1/2	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	WSI-2831-24
1 3/4	1 15/16	2	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	WSI-2831-32
1 3/4	1 15/16	3	1.7547	1.7507	1.9381	1.9371	1.7487	1.7471	WSI-2831-48
1 7/8	2 1/16	1	1.8747	1.8786	2.0621	2.0633	1.8721	1.8737	WSI-3033-16
1 7/8	2 1/16	2	1.8747	1.8786	2.0621	2.0633	1.8721	1.8737	WSI-3033-32
2	2 3/16	1	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	WSI-3235-16
2	2 3/16	1 1/2	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	WSI-3235-24
2	2 3/16	2	2.0057	2.0011	2.1883	2.1871	1.9981	1.9969	WSI-3235-32

³⁾ After press-fit. Testing methods ► Page 57

d1	d2	b1	d1 ³⁾		Housing bore		Shaft size		Part No.
			Max.	Min.	Max.	Min.	Max.	Min.	
2 1/4	2 7/16	2	2.2577	2.2531	2.4377	2.4365	2.2507	2.2489	WSI-3639-32

iglidur® X Chapter ► Page 245

d1	d2	b1	d1 ³⁾		Housing bore		Shaft size		Part No.
			Max.	Min.	Max.	Min.	Max.	Min.	
1/8	3/16	3/16	.1266	.1247	.1878	.1873	.1243	.1236	XSI-0203-03
1/8	3/16	5/16	.1266	.1247	.1878	.1873	.1243	.1236	XSI-0203-05
1/8	3/16	3/8	.1266	.1247	.1878	.1873	.1243	.1236	XSI-0203-06
3/16	1/4	3/16	.1888	.1869	.2503	.2497	.1865	.1858	XSI-0304-03
3/16	1/4	1/4	.1888	.1869	.2503	.2497	.1865	.1858	XSI-0304-04
3/16	1/4	3/8	.1888	.1869	.2503	.2497	.1865	.1858	XSI-0304-06
3/16	1/4	1/2	.1888	.1869	.2503	.2497	.1865	.1858	XSI-0304-08
1/4	5/16	1/4	.2518	.2495	.3128	.3122	.2490	.2481	XSI-0405-04
1/4	5/16	3/8	.2518	.2495	.3128	.3122	.2490	.2481	XSI-0405-06
1/4	5/16	1/2	.2518	.2495	.3128	.3122	.2490	.2481	XSI-0405-08
5/16	3/8	1/4	.3143	.3120	.3753	.3747	.3115	.3106	XSI-0506-04
5/16	3/8	3/8	.3143	.3120	.3753	.3747	.3115	.3106	XSI-0506-06
5/16	3/8	1/2	.3143	.3120	.3753	.3747	.3115	.3106	XSI-0506-08
3/8	15/32	1/4	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-04
3/8	15/32	5/16	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-05
3/8	15/32	3/8	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-06
3/8	15/32	1/2	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-08
3/8	15/32	5/8	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-10
3/8	15/32	3/4	.3768	.3745	.4691	.4684	.3740	.3731	XSI-0607-12
7/16	17/32	1/4	.4399	.4371	.5316	.5309	.4365	.4355	XSI-0708-04
7/16	17/32	1/2	.4399	.4371	.5316	.5309	.4365	.4355	XSI-0708-08
7/16	17/32	5/8	.4399	.4371	.5316	.5309	.4365	.4355	XSI-0708-10
7/16	17/32	3/4	.4399	.4371	.5316	.5309	.4365	.4355	XSI-0708-12
1/2	19/32	1/4	.5030	.5003	.5941	.5934	.4990	.4980	XSI-0809-04
1/2	19/32	3/8	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-06
1/2	19/32	1/2	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-08
1/2	19/32	5/8	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-10
1/2	19/32	3/4	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-12
1/2	19/32	1	.5024	.4996	.5941	.5934	.4990	.4980	XSI-0809-16
9/16	21/32	1/2	.5649	.5620	.6566	.6559	.5615	.5605	XSI-0910-08
9/16	21/32	5/8	.5649	.5620	.6566	.6559	.5615	.5605	XSI-0910-10
9/16	21/32	3/4	.5649	.5620	.6566	.6559	.5615	.5605	XSI-0910-12
5/8	23/32	1/4	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-04
5/8	23/32	3/8	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-06
5/8	23/32	1/2	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-08
5/8	23/32	5/8	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-10
5/8	23/32	3/4	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-12
5/8	23/32	1	.6274	.6246	.7192	.7184	.6240	.6230	XSI-1011-16
11/16	25/32	7/8	.6906	.6879	.7817	.7809	.6865	.6855	XSI-1112-14
3/4	7/8	3/8	.7532	.7499	.8755	.8747	.7491	.7479	XSI-1214-06

³⁾ After press-fit. Testing methods ► Page 57