

PRECISION FLAT AND SQUARE BAR STEEL WITH MACHINING ALLOWANCE, DIN 59350

Material:

1.2842 / 90 MnCrV
Cold worked steel

2923.2842.




we deliver original
BÖHLER
quality

Execution:

Thickness precision ground, width ground or milled, length machined

Note:

- = available in 500 mm and 1000 mm lengths
- = only available in 1000 mm lengths



2923.2842. Precision flat and square bar steel with machining allowance, DIN 59350

s	2.2	3.2	4.2	5.2	6.2	8.2	10.4	12.4	15.4	16.4	20.4	25.4	30.4	32.4	40.4	50.4	60.4	80.4	100.4
10.3	○	○	○	○	○	○													
10.4							●												
12.4								●											
15.3	○	○	○	○	○	○	○	○											
16.4										○									
20.3	○	○	●	●	●	●	●	●	●	○									
20.4											●								
25.3	○	○	●	●	●	●	●	●	●	○	●								
25.4												●							
30.3	○	○	●	●	●	●	●	●	●	○	●	●							
30.4													●						
32.3			○	○	○	○	○	○	○	○	○	○							
32.4														○					
40.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○					
40.4															●				
50.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○	●				
50.4																●			
60.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○	●	●			
60.4																	●		
63.3			○	○	○	○	○	○	○	○	○	○	○	○	○	○			
70.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○	●	●			
80.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○	●	●			
80.4																		●	
100.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○	●	●		●	
100.4																			●
120.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○	●	●		●	●
125.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○	●	●		●	●
150.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○	●	●		●	●
160.3			●	●	●	●	●	●	●	○	●	●	●	○	●	●		●	●
180.3			●	●	●	●	●	●	●	○	●	●	●	○	●	●		●	●
200.3	○	○	●	●	●	●	●	●	●	○	●	●	●	○	●	●		●	●
250.3			●	●	●	●	●	●	●	○	●	●	●	○	●	●		●	●
300.3						●	●	●	●	○	●	●	●					●	●

Ordering Code (example):

Precision flat and square bar steel with machining allowance, DIN 59350	=	2923.2842.
Width B	30.3 mm =	030.
Thickness S	2.2 mm =	002.
Length L	1000 mm =	1000
Order No	=	2923.2842. 030.002. 1000