




Mehrbereichs-Blindniet OPTO®

Serie 10.600





Aluminium / Stahl

Flachkopf <
offen <



EN AW - 5052 [AlMg2,5]



d	l +1		Nr.		
3,2	6,8	0,8 - 3,4	10.600.032.068	500	
	8,0	0,8 - 4,8	10.600.032.080	500	
	9,0	1,2 - 6,4	10.600.032.095	500	
	11,0	4,0 - 7,9	10.600.032.110	500	
	14,0	5,0 - 11,0	10.600.032.140	500	
d_k 6,4	d_m 1,8	k 1,0	3,3 mm		
4,0	6,0	1,0 - 3,0	10.600.040.060	500	
	9,5	1,2 - 6,4	10.600.040.095	500	
	12,7	4,0 - 9,5	10.600.040.127	500	
	16,9	6,0 - 12,5	10.600.040.169	500	
d_k 7,9	d_m 2,3	k 1,2	4,1 mm		

NEU

d	l +1		Nr.		
4,8	10,3	1,5 - 6,0	10.600.048.103	500	
	15,1	4,8 - 11,1	10.600.048.151	500	
	16,9	6,4 - 12,7	10.600.048.169	500	
	24,8	12,7 - 19,8	10.600.048.248	500	
	d_k 9,8	d_m 2,8	k 1,5	4,9 mm	
6,4	15,0	2,0 - 8,0	10.600.064.150	250	
	20,0	7,0 - 13,0	10.600.064.200	250	
	25,0	12,0 - 18,0	10.600.064.250	250	
d_k 12,7	d_m 3,7	k 1,9	6,5 mm		

NEU

NEU

NEU