

Interior installation

Earthing



Inserted screw nuts M12

Self-holding nuts with knurled ring for busbars E-Cu.
Hole diameter: 14.5 mm.

Packs of	Model No. SV
30	3591.060



PE/PEN combination angle E-Cu

for PE/PEN combinations

The PE/PEN combination, comprising busbars, combination angles and baying brackets, supports type-tested configurations as per IEC 61 439-1.

Thanks to the pre-assembled combination angles, baying brackets and busbars customised to match the enclosure width, assembly is time-saving with cost reduction.

Material:

E-Cu

Supply includes:

Assembly parts.

Technical specifications:

Tested short-circuit resistance

PE/PEN combination

- 30 x 5 mm:
I_{cw} 18 kA, 1 sec.
- PE/PEN combination 30 x 10 mm:
I_{cw} 30 kA, 1 sec.
- PE/PEN combination 40/80 x 10 mm:
I_{cw} 60 kA, 1 sec.



For busbars mm	Application		Size mm	Packs of	Model No. SV
	Form 2-4	Others			
30 x 5	■	■	30 x 5	4	9661.235
30 x 10	■	■	30 x 10	4	9661.230
40 x 10 and	■	-	40 x 10	4	9661.240
80 x 10	-	■	40 x 10	4	1 9661.200



Baying bracket E-Cu

For busbars mm	Length mm	Packs of	Model No. SV
30 x 5	95	4	9661.355
30 x 10	95	4	9661.350
40 x 10	88	4	9661.050
80 x 10	88	4	9661.150