




Aluminium / Edelstahl A2/A3

Senkkopf <  
offen <



2,4 - 3,0 mm EN AW - 5719 [AlMg5]  
3,0 - 5,0 mm EN AW - 5754 [AlMg3]

entsprechend DIN EN ISO 15978

d	l +1		Nr.	
---	---------	--	-----	--

<b>2,4</b>	6,0	1,5 - 4,0	10.702.240.060	500
------------	-----	-----------	----------------	-----

<b>dk</b> 4,5 +0,2	<b>dm</b> 1,45	2,5 mm	420 N	660 N
--------------------	----------------	--------	-------	-------

<b>3,0</b>	5,0	1,5 - 3,0	10.702.300.050	500
	6,0	1,5 - 4,0	10.702.300.060	500
	8,0	3,5 - 6,0	10.702.300.080	500
	10,0	5,0 - 7,5	10.702.300.100	500

NEU

<b>dk</b> 6,0 -0,4	<b>dm</b> 1,7	3,1 mm	660 N	900 N
--------------------	---------------	--------	-------	-------

<b>4,0</b>	6,0	1,5 - 3,5	10.702.400.060	500
	7,0	2,0 - 4,5	10.702.400.070	500
	8,0	2,0 - 5,5	10.702.400.080	500
	10,0	5,0 - 7,0	10.702.400.100	500
	12,0	6,5 - 9,0	10.702.400.120	500
	16,0	8,5 - 12,5	10.702.400.160	500

NEU

<b>dk</b> 7,5 -0,5	<b>dm</b> 2,0	4,1 mm	1120 N	1420 N
--------------------	---------------	--------	--------	--------

d	l +1		Nr.	
---	---------	--	-----	--

<b>5,0</b>	10,0	2,0 - 6,5	10.702.500.100	500
	12,0	6,0 - 8,0	10.702.500.120	500
	16,0	8,0 - 12,0	10.702.500.160	500
	20,0	12,0 - 15,5	10.702.500.200	500

NEU

<b>dk</b> 9,3 -0,5	<b>dm</b> 2,7	5,1 mm	1650 N	2000 N
--------------------	---------------	--------	--------	--------