



Data in mm

Structure – part no.

E B ... M-06 HT



- High Temperature
- Dimension Metric
- Thread L = Left-hand R = Right-hand
- Housing (female thread)
- Material

igubal® – Rod End Bearings:

- for temperatures up to 200 °C
- Maintenance-free, self-lubricating
- High strength under impact loads
- Very high tensile strength for varying loads
- Compensation for alignment errors
- Compensation for edge loads
- Resistant to dirt, dust and lint
- Resistant to chemicals
- under water use
- High vibration dampening capacity
- Suitable for rotating, oscillating and linear movements
- Lightweight
- Dimensional series K according to standard DIN ISO 12240



Material

Housing: iguton G
 ► Page 70.6
 Spherical Bearing: iglidur® X
 ► Chapter 6

Dimensions [mm]

igubal® – Rod End Bearings EBRM HT/EBLM HT

Part Number		d1	d2	d3	d4	d5	C1	B	h1	l3	l4	W	Max. pivot angle
		E10											
EBRM-06 HT	EBLM-06 HT	6	21	M06	11,0	13	4,4	6	30	12	40,5	SW11	27°
EBRM-08 HT	EBLM-08 HT	8	24	M08	13,0	16	6,0	8	36	16	48,0	SW14	24°
EBRM-10 HT	EBLM-10 HT	10	29	M10	15,0	19	7,0	9	43	18	57,5	SW17	24°
EBRM-12 HT	EBLM-12 HT	12	34	M12	18,0	22	8,0	10	50	20	67,0	SW19	21°

Available from stock

Rod End Bearings
mm EBRM HT/EBLM HT

Phone +49 - 22 03 - 96 49-145
Fax +49 - 22 03 - 96 49-334

