

Air/water heat exchangers

Wall-mounted, useful cooling output 500 W, water-carrying parts V4A (1.4571)

Model No. SK	3363.504 ¹⁾	3363.104 ¹⁾	Page
Thermostat (factory setting +35°C)	e-Comfort controller	■	–
	Basic controller	–	■
Useful cooling output	L 35 W 10, 400 l/h	500 W	
Rated operating voltage V, Hz	230, 1~, 50/60		
External transformer	–	–	
Dimensions mm	W x H x D	280 x 550 x 120	

Rated current max.	0.17 A/0.18 A
Pre-fuse T	4.0 A
Cooling medium	Water (for specifications see Internet; user manual)
Water inlet temperature	+1°C to +30°C
Permissible operating pressure p. max.	1 to 10 bar
Operating temperature and setting range	+1°C to +70°C
Protection category to IEC 60 529	IP 55 ²⁾
Duty cycle	100%
Type of connection	Plug-in terminal strip
Water connection	Quick-release fastener system ³⁾
Weight	12 kg
Air throughput of fan (unimpeded air flow)	270/320 m ³ /h

Accessories	Packs of			
Door-operated switch	1	4127.010	4127.010	684
SK BUS system	1	3124.100	–	477
Interface board	1	3124.200	–	477
Condensate hose	1	3301.612	3301.612	485
Flow regulator valve	1		see page 486	

¹⁾ Extended delivery times.

²⁾ IP 65 available on request.

³⁾ Threaded adaptor for quick-release fastener available on request.

Special voltages available on request. We reserve the right to make technical modifications.

Wall-mounted, useful cooling output 750 W, water-carrying parts V4A (1.4571)

Model No. SK	3364.504 ¹⁾	3364.104 ¹⁾	Page
Thermostat (factory setting +35°C)	e-Comfort controller	■	–
	Basic controller	–	■
Useful cooling output	L 35 W 10, 400 l/h	750 W	
Rated operating voltage V, Hz	230, 1~, 50/60		
External transformer	–	–	
Dimensions mm	W x H x D	280 x 550 x 120	

Rated current max.	0.2 A/0.19 A
Pre-fuse T	4.0 A
Cooling medium	Water (for specifications see Internet; user manual)
Water inlet temperature	+1°C to +30°C
Permissible operating pressure p. max.	1 to 10 bar
Operating temperature and setting range	+1°C to +70°C
Protection category to IEC 60 529	IP 55 ²⁾
Duty cycle	100%
Type of connection	Plug-in terminal strip
Water connection	Quick-release fastener system ³⁾
Weight	15 kg
Air throughput of fan (unimpeded air flow)	270/320 m ³ /h

Accessories	Packs of			
Door-operated switch	1	4127.010	4127.010	684
SK BUS system	1	3124.100	–	477
Interface board	1	3124.200	–	477
Condensate hose	1	3301.612	3301.612	485
Flow regulator valve	1		see page 486	

¹⁾ Extended delivery times.

²⁾ IP 65 available on request.

³⁾ Threaded adaptor for quick-release fastener available on request.

Special voltages available on request. We reserve the right to make technical modifications.