

TopTherm wall-mounted cooling units "Blue e"



Climate control accessories Page 369 Therm software Page 385

Temperature control:

- e-Comfort controller (factory setting +35°C)

Protection category IP to IEC 60 529:

- External circuit IP 34
- Internal circuit IP 54

Supply includes:

- Nano-coated condenser
- Integral electric condensate evaporation
- Fully wired ready for connection (plug-in terminal strip)
- Drilling template
- Assembly parts

Note:

- Full installation not supported on model numbers 3332.XXX

Approvals:


Available on the Internet

Performance diagrams:

Available on the Internet

Technical details:

Available on the Internet



Output class 2000 W

Model No.	Packs of	3328.500	3328.510	3328.540	3328.600	3328.640	Page
Material	Sheet steel	■	■	■	-	-	
	Stainless steel	-	-	-	■	■	
Colour	RAL 7035	■	■	■	-	-	
Total cooling output 50 Hz L35 L35 to DIN EN 14511 kW		2.2	2.2	2.2	2.2	2.2	
Total cooling output 50/60 Hz L35 L35 kW		2.2 / 2.56	2.2 / 2.56	2.2 / 2.55	2.2 / 2.56	2.2 / 2.55	
Total cooling output 50/60 Hz L35 L50 kW		1.82 / 1.95	1.82 / 1.95	1.65 / 1.89	1.82 / 1.95	1.65 / 1.89	
Rated operating voltage V, ~, Hz		230, 1~, 50/60	115, 1~, 50/60	400, 3~, 50 460, 3~, 60	230, 1~, 50/60	400, 3~, 50 460, 3~, 60	
Width (B) mm		400	400	400	400	400	
Height (H) mm		1580	1580	1580	1580	1580	
Depth (T) mm		295	295	295	295	295	
Rated current max. A		6.1 / 6.6	13.4 / 14.8	2.8 / 3.3	6.1 / 6.6	2.8 / 3.3	
Start-up current A		20 / 22	40 / 38	6.8 / 7.8	20 / 22	6.8 / 7.8	
Pre-fuse A		16	-	-	16	-	
Transformer circuit-breaker A		-	18...25	-	-	-	
Motor circuit-breaker A		-	-	6.3...10	-	6.3...10	
Power consumption P _{el} 50/60 Hz L35 L35 kW		0.92 / 1.03	0.92 / 1.03	0.92 / 1.15	0.92 / 1.03	0.93 / 1.15	
Power consumption P _{el} 50/60 Hz L35 L50 kW		1.06 / 1.23	1.06 / 1.23	1.15 / 1.4	1.06 / 1.23	1.15 / 1.4	
Operating temperature range		+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	
Setting range		+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	
Energy efficiency ratio (EER) 50 Hz L35 L35 to DIN EN 14511		2.4	2.4	2.2	2.4	2.2	
Refrigerant g		R134a, 950	R134a, 950	R134a, 950	R134a, 950	R134a, 950	
Permissible operating pressure (p. max.) bar		28	28	28	28	28	
Air throughput of fans (unimpeded air flow), internal circuit / external circuit m ³ /h		980 / 980	980 / 980	900 / 900	980 / 980	900 / 900	
Weight kg		66.0	73.0	67.0	66.0	67.0	
Accessories							
Filter mats	3 pc(s).	3286.400	3286.400	3286.400	3286.400	3286.400	369
Metal filters	1 pc(s).	3286.410	3286.410	3286.410	3286.410	3286.410	370