

# 铰链 不锈钢蝶形铰链



框架部品及配件

## 选型指南


举例	型号	孔数
	Code No.	
标准	HY11S 5 - 2	

Code	类型	材质	表面处理
HY11S	圆孔型	SUS304	抛光
HY12S	锥孔型	SUS304	


### ■ 不锈钢蝶形铰链



HY11S (圆孔型)



HY12S (锥孔型)



型号		单侧孔数	容许负载		重量 g	La	W	K	P	J	S
Code	No.		kg	N							
HY11S HY12S	5	2	9	88	43	41	36	8	25	7.5	21
		3	11	108	70	66					
	6	2	12	117	60	48	48	9	30	8	32
		3	15	146.5	98	78					
	8	2	25	245	129	59	62	11	37	10	42
		3	37.5	372	230	96					
845	2	30	293.5	190	70	80	13.5	43	16.5	47	
	3	40	392	325	113						

容许负载是使用2个时的数值。

型号		单侧孔数	HY11S							HY12S					
Code	No.		N	T	E	R	CR	D	N		T	E	R	CR	D
									通孔	铤锥孔					
HY11S HY12S	5	2	5.5	2	4.6	4.6	7.5	5	5.5	8.6 (M4用)	2	4.6	4.6	4	5
		3													
	6	2	6.5	3	5.6	5.6	10	6	6.5	10.6 (M5用)	3	6.1	6.1	5	6
		3													
	8	2	6.5	3	5.6	5.6	10	6	6.5	10.6 (M5用)	3	6.1	6.1	5	6
		3													
845	2	6.5	3	5.6	5.6	10	6	6.5	10.6 (M5用)	3	6.1	6.1	5	6	
	3														

支柱

支柱座

支柱  
固定夹

触摸屏  
支架

支脚

脚轮

拉手

手柄·  
旋钮

手轮

铰链

门部件