


圆形拉手 标准内装型

选型指南

举例	型号	- L - H	
标准	Code D	100	50
		LS64C	10 - 100 - 50



Code	材质	表面处理
LS64C	SUM22L	镀铬
LS64CB	或SUM24L	四氧化三铁保护膜
LS64AD	铝合金	抛光
LS64A		本色阳极氧化处理
LS64AC		喷塑(黑色)



型号		L	H	L ₁	M	容许负载 (N)	
Code	D						
LS64C LS64CB LS64AD LS64A LS64AC	10	80	27	90	5	2500	
			50				
		100	27	110			
			50				
		110	27	120			6
			30				5
			50				
		120	27	130	6		
			30				
			50				
		125	27	135	5		
			50				
	27						
	160	27	170				
		50					
	200	27	210				
50							
250	27	260					
	50						
12	150	40	162	8			
		75					
		40			200		
		75					
	238	40	250				
		75					
	288	40	300				
		75					

支柱

支柱座

支柱
固定夹

触摸屏
支架

支脚

脚轮

拉手

手柄·
旋钮

手轮

铰链

门部件