

Power supply

Socket strips

Energy-Box, 3 U, 482.6 mm (19')

Technical specifications:

- Depth-adjustable top hat rail for installed equipment to DIN 43 880, sizes 1 – 3 (e.g. to accommodate built-in sockets, circuit-breakers etc.).
- Cable clamping rear, one N and one PE rail on insulated base/plinth
- Plastic hood including extension cover (UL 94-V0)
- Maximum accommodation capacity of 22 HP (22 x 18 mm = 396 mm)
- Enclosure height: 3 U
- Enclosure depth: 155 mm
- Overall installation depth with C rail: 155 mm
- Dimensions:
W x H x D: 483 x 132.5 x 155 mm

Colour:

- RAL 7035

Supply includes:

- 1 Energy-Box with fitted N and PE rails and brush strip
- 4 connection clamps, 35 mm²
- 18 connection clamps, 16 mm²
- 2 blanking covers
- 12 clips for cable strain relief
- Identification strips, self-adhesive

Packs of	U	Model No.
1 pc(s).	3	7480.035

Photograph shows a configuration example with equipment not included in the scope of supply



Energy-Box, 3 U, 482.6 mm (19')

Pull-out

Technical specifications:

- Depth-adjustable top hat rail for snap-in attachment of installed equipment to DIN 43 880 in sizes 1 – 3 (e.g. to accommodate built-in sockets, circuit-breakers etc.) or entire installation assemblies
- Cable clamping at rear
- Two power distribution rails with connection clamps on insulated base/plinth
- Plastic hood including extension cover
- Maximum accommodation capacity of 22 HP (22 x 18 mm = 396 mm)
- Enclosure height: 3 U
- Enclosure depth: 223 mm
- Maximum extension: 220 mm
- Dimensions:
W x H x D: 483.5 x 132 x 223 mm

Colour:

- RAL 7035

Supply includes:

- 1 Energy-Box with fitted N and PE rails and brush strip
- 4 connection clamps, 35 mm²
- 18 connection clamps, 16 mm²
- 2 blanking covers
- 12 clips for cable strain relief
- Identification strips, self-adhesive

U	Model No.
3	7480.300

Photograph shows a configuration example with equipment not included in the scope of supply

