


Human/machine interface

Handles, external mounting accessories/connection components



Clipboard

For securing operating instructions or plans (A4 size) at eye level. Prepared for mounting on the right-hand side; mounting on the left is also possible by unscrewing and moving the clip part. For mounting purposes, a straight tube length of ≥ 200 mm, $\varnothing 20$ mm or $\varnothing 25$ mm, is required.

Material:

Sheet steel, RAL 7035
Clip: Aluminium, natural-anodised.

Width mm	Height mm	Model No. CP
225	315	6013.000

Clipboard in conjunction with Command Panel VIP 6000:

European patent no. 0 839 093 with validity for DE, FR, GB, IT



Also required:

Handle set SZ 2389.000, see page 1116
or
Handle set for Comfort Panel, see page 1115
or
Handle set for VIP 6000, see page 1116
or
Handle set for Optipanel, see page 1115
or
U handle CP 6107.200, see page 1117.



Display board with wall bracket

To accommodate test plans, documents etc. in A4 format.

Installation:

- On surfaces,
- On a 25 mm pitch pattern of the TS frame or rail system,
- On handle set $\varnothing 20$ mm or $\varnothing 25$ mm.

Supply includes:

10 display boards, wall brackets and assembly parts.

Packs of	Model No. CP
1 set	6013.100



Accessories:

Handle set SZ 2389.000, see page 1116
or
Handle set for Comfort Panel, see page 1115
or
Handle set for VIP 6000, see page 1116
or
Handle set for Optipanel, see page 1115
or
U handle CP 6107.200, see page 1117.



Enclosure surface connector

To accommodate:

- Support for keyboards (SM 2383.000)
- Optipanel keyboard housing for front panel width = 482.6 mm (19") CP 6384.009. Please state front panel height and installation depth (50 or 100 mm) in addition to Model No.

Material:

Extruded aluminium section, natural-anodised, Side cover, sheet steel RAL 7024.

Supply includes:

Assembly parts.


Packs of	Model No. SM
1 set	2383.010

Note:

Other widths available on request.



Mounting on surfaces



Mounting underneath surfaces

