

Viewing windows/operating panels

Viewing window

Stainless steel

Equipped as standard with internal 130° hinges and all-round seal.

The double-bit lock insert may be exchanged for 27 mm lock inserts, type A, and Ergoform-S handle 2452.000.

Material:

- Stainless steel 1.4301 (AISI 304)
- Single-pane safety glass

Protection category to IEC 60 529:

- IP 54


Supply includes:

- Assembly components

Height inches (mm)	Width inches (mm)	Depth inches (mm)	Model No.
24 (600)	21 (522)	2 (38)	2793.560

Accessories:

- Lock inserts 27 mm, type A, see page 488
- Ergoform-S handle 2452.000, see page 486



Window kit

Can be installed in most Rittal enclosures of suitable dimensions. The required hardware is included in the window kit. Oil-tight seals ensure a good all-round seal.

Material:

- Carbon steel: 2.0 mm
- Stainless steel 1.4301 (AISI 304): 2.0 mm

Surface finish:

- Carbon steel: Dipcoat-primed, powder-coated on the outside, textured paint
- Stainless steel: Brushed

Color:


- Carbon steel: RAL 7035

Protection category NEMA:

- Carbon steel: NEMA 12, 3R, 4
- Stainless steel: NEMA 12, 3R, 4X

Note:

- When determining the dimensions for the window, allow clearance for seals, retainers, door reinforcement, wiring plan pocket, door handles, locking rod and other parts to be fastened to the door or cover.



Window height inches (mm)	Window width inches (mm)	Frame height inches (mm)	Frame width inches (mm)	Model No.	Model No. US	Model No.	Model No. US
				Carbon steel		Stainless steel 1.4301 (AISI 304)	
5 (127)	3 (76)	8 (191)	6 (140)	8018.444	WK0503C	8018.445	WK05034
9 (229)	6 (140)	11 (292)	8 (203)	8018.447	WK0905C	8018.448	WK09054
13 (330)	8 (203)	16 (394)	11 (267)	8018.453	WK1308C	8018.454	WK13084
17 (432)	11 (279)	19 (495)	14 (343)	8018.459	WK1711C	8018.460	WK17114
23 (584)	15 (381)	26 (648)	18 (445)	8018.462	WK2315C	8018.463	WK23154