

## SERIES 72

### SIGMA ELASTIC RUBBER WHEELS AND ALUMINIUM CENTRE



#### Wheel description

Sigma Elastic rubber tread; hardness 70 +/-3 Shore A. Aluminium centre.

#### Hub

The housing is obtained by moulding and contains ball bearings series Z. The hub is available also without bearings.

**Diameters: 100-250 mm**

**Carrying capacity: 180-500 daN**

#### Fittings with swivel, fixed and swivel with brake brackets



#### Standard duty brackets type NL

Max. carrying capacity 400 daN – available diameters 80-300 mm

Models available: with top plate fastening, with bolt hole

Suitable brakes: front-locking and central (hexagonal) brake systems



#### Medium duty brackets type M

Max. carrying capacity 500 daN – available diameters 150-200 mm

Models available: with top plate fastening

Suitable brakes: adjustable front-locking brake



#### Medium-heavy duty brackets type P

Max. carrying capacity 750 daN – available diameters 80-200 mm

Models available: with top plate fastening

Suitable brakes: front-locking and adjustable rear-locking brake systems



#### Electro-welded brackets type EE MHD

Max. carrying capacity 3500 daN – available diameters 100-400 mm

Top plate fastening. Adjustable rear-locking brake systems



#### Paired electro-welded brackets type EEG MHD – EEG HD

Max. carrying capacity 3500 daN – available diameters 100-250 mm

Top plate fastening.

#### Uses

##### Environments

Suitable for humid environments, with medium-harsh chemicals; not suitable for applications where organic solvents and hydrocarbons are present.

Usage temperatures: from da -20 °C a +70 °C.

##### Floors



##### Handling

