

RiLine Class fuse elements



Busbar systems Page 276 – 279 **Connection system** Page 280 – 282 **Component adaptors** Page 283 – 289 **Accessories** Page 310 – 325

Material:

- Polyamide (PA 6).
- Fire protection corresponding to UL 94-V0
- Contact tracks: Electrolytic copper, silver-plated

Approvals:

- UL 4248-1/UL 4248-8
- CSA C22.2 No. 4248.107/CSA C22.2 No. 4248.8-07

Technical information:

Available on the Internet.

Detailed drawings:

Available on the Internet.

Colour:

- Chassis: RAL 7035
- Cover: RAL 7035/7001

Fuse holder 61 – 400 A (3-pole)

| Fuse type (class) | Packs of | J | J | J |
|------------------------------------|----------|-----------------|-------------------|-----------------------|
| Rated operating current | | 61 – 100 A | 101 – 200 A | 201 – 400 A |
| Rated operating voltage | | 600 V~ | 600 V~ | 600 V~ |
| Fuse standard | | UL 4248-8 | UL 4248-8 | UL 4248-8 |
| Fuse size mm | | 29 x 118 | 41 x 146 | 54 x 181 |
| Cable outlet | | top/bottom | top/bottom | top/bottom |
| Type of connection | | Box terminal | Box terminal | Box terminal |
| Connection of round conductors | | AWG 2 – MCM 300 | AWG 3/0 – MCM 600 | AWG 3/0 – MCM 600 |
| Width mm | | 184 | 210 | 250 |
| Height mm | | 288 | 288 | 328/353 ¹⁾ |
| Approvals | | | | |
| For bar systems | | | | |
| Bar centre distance mm | | 60 | 60 | 60 |
| For bar thickness mm | | 5/10 | 5/10 | 5/10 |
| Model No. SV | 1 | 9345.100 | 9345.200 | 9345.400 |
| For mounting plate assembly | | | | |
| Model No. SV | 1 | 9345.110 | 9345.210 | 9345.410 |

¹⁾ 328 mm (SV 9345.400), 353 mm (SV 9345.410)