


SERIES 75



“TR” POLYURETHANE TRANSPALLET ROLLERS STEEL CENTRE, SWIVEL TOP PLATE BRACKET TYPE EE MHD

Roller description




Tread: “TR” polyurethane tread, hardness 95 +/- 3 Shore A, excellent rolling resistance and elasticity, good resistance to wear and to tearing.

Centre: weldless steel centre.

Hub: The housing is obtained by moulding and turning and contains ball bearings series Z. The hub is available also without bearings.

Bracket description

Bracket EE Medium Heavy Duty (max. load capacity 900 daN)



- 1) **Plate:** forged steel with integrated pin
 - 2) **Fork:** drawn sides electrowelded to the flange
 - 3) **Swivel actions:** axial ball bearing and taper roller bearing
 - 4) **Lubricator**
 - 5) **Nut anti-loosening system**
- Finish:** electrolytic galvanisation
Fitting: top plate