

TopTherm roof-mounted cooling units "Blue e"

Output class 3000 – 4000 W

Model No.	Packs of	3386.540	3386.640	3387.540	3387.640	Page
Material	Sheet steel	■	–	■	–	
	Stainless steel	–	■	–	■	
Colour	RAL 7035	■	–	■	–	
Total cooling output 50 Hz L35 L35 to DIN EN 14511 kW		3	3	3.8	3.8	
Total cooling output 50/60 Hz L35 L35 kW		3 / 3.3	3 / 3.3	3.8 / 4	3.8 / 4	
Total cooling output 50/60 Hz L35 L50 kW		2.2 / 2.5	2.2 / 2.5	3.05 / 3.3	3.05 / 3.3	
Rated operating voltage V, ~, Hz		400, 3~, 50 460, 3~, 60	400, 3~, 50 460, 3~, 60	400, 3~, 50 460, 3~, 60	400, 3~, 50 460, 3~, 60	
Width mm		796	796	796	796	
Height mm		470	470	470	470	
Depth mm		580	580	580	580	
Rated current max. A		3.4 / 3.4	3.4 / 3.4	3.9 / 3.9	3.9 / 3.9	
Start-up current A		8 / 9	8 / 9	17 / 19	17 / 19	
Motor circuit-breaker A		6.3...10	6.3...10	6.3...10	6.3...10	
Power consumption P _{el} 50/60 Hz L35 L35 kW		1.17 / 1.48	1.17 / 1.48	1.59 / 2.03	1.59 / 2.03	
Power consumption P _{el} 50/60 Hz L35 L50 kW		1.42 / 1.76	1.42 / 1.76	1.84 / 2.31	1.84 / 2.31	
Operating temperature range		+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	+10°C...+55°C	
Setting range		+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	+20°C...+55°C	
Energy efficiency ratio (EER) 50 Hz L35 L35 to DIN EN 14511		2.56	2.56	2.38	2.38	
Refrigerant g		R134a, 1600	R134a, 1600	R134a, 1600	R134a, 1600	
Permissible operating pressure (p. max.) bar		28	28	28	28	
Air throughput of fans (unimpeded air flow), internal circuit / external circuit m ³ /h		1280 / 3450	1280 / 3450	1420 / 3870	1420 / 3870	
Weight kg		70.0	70.0	77.0	77.0	
Accessories						
Filter mats	3 pc(s).	3286.600	3286.600	3286.600	3286.600	369
Metal filters	1 pc(s).	3286.610	3286.610	3286.610	3286.610	370
Door-operated switch	1 pc(s).	4127.010	4127.010	4127.010	4127.010	639
Air duct system	1 pc(s).	3286.970	3286.970	3286.970	3286.970	374
Stoppers	2 pc(s).	3286.980	3286.980	3286.980	3286.980	376

