

## Bell suction cup (round)

### SAX 30 ED-85 G1/4-IG

Part no.:10.01.19.00179

<https://www.schmalz.com/10.01.19.00179>

Homepage > Vacuum Technology for Automation > Vacuum Components > Vacuum Suction Cups > Suction Cups for Handling Sheet Metal >

Bell-Shaped Suction Cups SAX > SAX 30 ED-85 G1/4-IG

## Bell suction cup (round) for best adaptation to strongly curved surfaces



Size: 30


Suction cup material: Elastodur

Material hardness: 85 °Sh

Vacuum connection: G1/4"-F

Nipple material: Brass, nickel-plated

## Design Data



Attribute	Value
dn	6.75 mm
Dmax(S)	35.2 mm
Ds	31.7 mm
G1	G1/4"-F
H	32.8 mm
LG1	15 mm
SW1	22 mm
Z (Stroke)	4.5 mm

## Technical Data

### Contact to Schmalz

J. Schmalz GmbH | Johannes-Schmalz-Straße, 72293 Glatten, Deutschland | +49 7443 2403-102 | [customercenter@schmalz.de](mailto:customercenter@schmalz.de)

## Bell suction cup (round)

### SAX 30 ED-85 G1/4-IG

Part no.:10.01.19.00179

<https://www.schmalz.com/10.01.19.00179>



Attribute	Value
Suction force (-600mbar)	39 N
Lateral force	38 N
Lateral force (oily surface)	41 N
Volume	3.2 cm <sup>3</sup>
Curve radius (min) (convex)	18 mm
Size	30
Connection	G1/4"-F
Number of folds	0
Suction cup material	Elastodur
Material hardness [Shore A]	85 Shore A
Weight	37.3 g
Product family	SAX

---

---